

EOS MaragingSteel MS1

EOS MaragingSteel MS1 is a tool steel powder intended for processing on EOS DMLS™ systems.

This document provides information and data for parts built using

- EOS Powder: EOS MaragingSteel MS1 (EOS art.-no. 9011-0016)
- EOS Laser Sintering Machine: EOS M400-4
 - Ceramic Blade (EOS art.-no. 300007622)
 - DirectBase S40 Building Platform (EOS art.-no. 300000729)
 - Nitrogen atmosphere
 - 63 μm mesh for powder sieving recommended (EOS art.-no. 9044-0032 for IPCM M Extra Sieving Module or EOS art.-no. 200001059 for IPM M Powder Station L)
 - EOSYSTEM v. 2.5* or higher
- EOS Software:
 - EOSPRINT v. 1.6 (EOS art.-no. 7501-4031) or higher
- EOS Process:
 - MS1 ParameterEditor (EOS art.-no. 7500-3068)
 - Name of the Default Job: MS1_040_FlexM404_100.eosjob

Description

EOS MaragingSteel MS1 has a chemical composition following US classification 18% Ni Maraging 300, European 1.2709 and German X3NiCoMoTi 18-9-5. This kind of steel is characterized by having very good mechanical properties, and being easily heat-treatable using a simple thermal age-hardening process to obtain excellent hardness and strength.

Parts built from EOS MaragingSteel MS1 are easily machinable after the building process and can be easily post-hardened to more than 50 HRC by age-hardening at 490 °C (914 °F) for 6 hours. In both as-built and age-hardened states the parts can be machined, spark-eroded, welded, micro shot-peened, polished and coated if required.

EOS GmbH - Electro Optical Systems

Telephone: +49 (0)89 / 893 36-0 Telefax: +49 (0)89 / 893 36-285 Internet: www.eos.info

^{*} EOSYSTEM v. 2.6 or higher enables EOSPRINT v. 2.0 (EOS art.-no. 7012-0119) or higher usage



Due to the layerwise building method, the parts have a certain anisotropy, which can be reduced or removed by appropriate heat treatment - see Technical Data for examples.

Technical Data

Powder properties

The chemical composition of the powder (wt-%):

Material composition

Element	Min	Max
Fe	Balance	
Ni	17.00	19.00
Со	8.50	9.50
Мо	4.50	5.20
Ti	0.60	0.80
Al	0.05	0.15
Cr	-	0.50
Cu	-	0.50
С		0.03
Mn		0.10
Si		0.10
Р		0.01
S		0.01

Max. particle size

[-]	
> 63µm [1]	max 0.5 wt%

^[1] Sieve analysis according to ASTM B214.

EOS GmbH - Electro Optical Systems

Internet: <u>www.eos.info</u>

CR543 / 06-18

EOS MaragingSteel MS1 M400-4



General process data

Layer thickness	40 μm	
Volume rate [2]	Up to 4 x 4.2 mm ³ /s (4 x 15.1 cm ³ /h)	

^[2] The volume rate is a measure of build speed during laser exposure of the skin area. The total build speed depends on this volume rate and other factors such as exposure parameters of contours, supports, up- and downskin, recoating time, Home-In or LPM settings, job design (load, part geometry or overlap settings).

Physical and chemical properties of parts

Part density [3]	8.0-8.1 g/cm3
Part accuracy [4]	
Small parts	
Large parts	Approx ± 0.1 %
Min. wall thickness [5]	Approx. 0.3 - 0.4 mm
Surface roughness after shot peening [6]	
	Ra 4-6.5 μm; Rz 20-50 μm

^[3] Weighing in air and water according to ISO 3369.

- [5] Mechanical stability is dependent on geometry (wall height etc.) and application.
- [6] Measurement according to ISO 4287. Due to the layerwise building the roughness strongly depends on the orientation of the surface, for example sloping and curved surfaces exhibit a stair-step effect.

Hardness in heat treated status [7]

Hardness Rockwell C [8]	50-57 HRC

^[7] Heat treatment procedure: Ageing temperature 490 °C 6 hours, air cooling

EOS GmbH - Electro Optical Systems

Robert-Stirling-Ring 1

^[4] Based on users' experience of dimensional accuracy for typical geometries, e.g. \pm 50 μ m when parameters can be optimized for a certain class of parts or \pm 0.1% when building a new kind of geometry for the first time or building larger parts. Part accuracy is subject to appropriate data preparation and postprocessing.

^[8] Rockwell C (HRC) hardness measurement according to EN ISO 6508-1 on polished surface



Tensile data at room temperature [9,10]

	As built	
	Horizontal	Vertical
Ultimate tensile strength, Rm	1200 MPa	1200 MPa
Yield strength, Rp0.2	1020 MPa	1050 MPa
Elongation at break, A [11]	13 %	11 %

Heat treated [7]

	Horizontal	Vertical
Ultimate tensile strength, Rm	2060 MPa	2080 MPa
Yield strength, Rp0.2	1990 MPa	2010 MPa
Elongation at break, A [11]	4 %	3 %

^[9] Tensile testing according to. ISO 6892-1 B10, proportional test pieces, diameter of the neck area 5 mm, original gauge length 25 mm.

^[10] The numbers are average values determined from samples with horizontal and vertical orientation respectively

^[11] Elongation values depend on the thermal load of particular job layout as well as the positioning on the platform.



Abbreviations

Min. Minimum

Max. Maximum

Approx. Approximately

Wt. Weight

The quoted values refer to the use of this material with above specified type of EOS DMLS system, EOSYSTEM software version, parameter set and operation in compliance with parameter sheet and operating instructions. Part properties are measured with specified measurement methods using defined test geometries and procedures. Further details of the test procedures used by EOS are available on request. Any deviation from these standard settings may affect the measured properties.

The data correspond to EOS knowledge and experience at the time of publication and they are subject to change without notice as part of EOS' continuous development and improvement processes.

EOS does not warrant any properties or fitness for a specific purpose, unless explicitly agreed upon. This also applies regarding any rights of protection as well as laws and regulations.

EOS®, EOSINT®, DMLS®, DirectTool® and DirectPart® are registered trademarks of EOS GmbH.

© 2018 EOS GmbH – Electro Optical Systems. All rights reserved.